


# Kleen-Flo® Variable Speed Probe Assembly

## Custom Probe Order Form

Standard Probe Assembly is 3 Floats ~ Maximum is 5 Activation Points



### Standard Configuration



- ~ 1st Switch - Red
- ~ 2nd Switch - Yellow
- ~ 3rd Switch - Blue
- ~ 4th - Green
- ~ Top Switch - 2 Brown (Isolated)
- ~ Common - Black

- *Need measurement of exact location of each additional float for proper placement.*
- *Measure from bottom up for your float(s) position(s) in inches.*

Date:	PO#:
Name:	
Phone:	Fax:
Float Assembly with Probe Holder: #20022-1½" or #20023-2" (Please Circle One)	
Other and/or Notes:	

- 20004** - Additional Floats, Includes: 2 clips and float
- 20010** - Complete probe assembly for BM, *with Reed Switch, Junction box and New Style Float*
- 20012** - Stainless rod only for float style probe, 29" long
- 20014** - Junction box for BM style probe
- 20015** - Junction Box, with large cord grip
- 20016** - Clip
- 20018** - Stainless steel collar, *5/16" ID - 5/8" OD - 5/16" width*

- 20019** - 1½" long insert for reed switch
- 20020** - Reed switch for plastic float probe
- 20022** - Kleen-Flo Variable Speed Float Assembly, *with 1½" ID probe holder*
- 20023** - Kleen-Flo Variable Speed Float Assembly, *with 2" ID probe holder*
- 20025** - Reed switch for stainless float probe
- 20030** - Stainless float ONLY

